


## Indoor Riser Interconnect Cable with Armor-Tek™ (ICRK)

### APPLICATION

Leviton riser-rated Indoor Interconnect Cables are designed specifically for patch cables and riser structured cabling applications. Armor-Tek Interlocking Armor is wound around the cable core. A riser-rated sheath is extruded around the interlocking armor. Black jacketed and core waterblocked cables with 2 or 4 fibers are available upon request for indoor/outdoor installations.



### BENEFITS

- Eliminates the need for conduit or plenum innerduct
- Significant cost savings in both materials and labor up to 25%
- Accommodates last minute relocations or pathway changes
- Provides a higher concentration of cables in an area than conduit
- Armor provides crush protection and protection from rodent attacks

### FEATURES

- Indoor/outdoor versions feature UV and fungus resistant jacketing
- Flexible 900 µm tight buffered construction
- High tensile strength cost-saving design, easy to install and terminate
- Single-mode, multimode, and hybrid designs available
- Available in low-smoke zero halogen design
- This design incorporates 2 or 4 tight buffered (900 µm) optical fibers within the core cable
- Interlock armor and an outer jacket are added over the cable core
- No Buffer Tube Fanout kits are required
- Direct termination is enabled
- OFCR rated

### STANDARDS & REGULATIONS

- EN 50173; ISO/IEC 11801
- ANSI/ICEA S-83-596; ANSI/TIA-568.3-D; Telcordia GR-409
- ETHERNET: 10BASE – 40GBASE (10BASE, 100BASE, 1000BASE, 10GBASE, 40GBASE, 100GBASE, 400GBASE)
- Fibre Channel: 1G-FC – 128GFC (1, 2, 4, 8, 16, 32, 128 GFC)
- SONET: OC-1 – OC-768 (OC -1, 3, 12, 24, 48, 192, 768)
- SDH: STM-0 – STM-256 (STM-0, 1, 4, 16, 64, 256)
- OTN: OTU-1 – OTU4 (OTU1, 2, 2e, 2f, 3, 3e2, 4)
- CPRI: CPRI-1 – CPRI-9 (CPRI-1, 2, 3, 4, 5, 6, 7, 7a, 8, 9)
- PON (SMF only): RFoG, APON, BPON, EPON, GPON, WDM-PON, NG-PON

### COUNTRY OF ORIGIN

USA

### WARRANTY INFORMATION

For Leviton product warranties, go to [leviton.com/warranty](http://leviton.com/warranty)

# PRODUCT SPECIFICATIONS

## Indoor Riser Interconnect Cable with Armor-Tek™ (ICRK)



Indoor Riser Interconnect Cable with Armor-Tek™

### CHARACTERISTICS

#### Construction

Type of Cable	Tight Buffered (TB)
Jacket Material	Riser
Armor Type	Aluminum Interlock

#### Usage Characteristics

RoHS Complaint	Yes
----------------	-----

### TECHNICAL DATA - PHYSICAL

Fiber	Part Number Prefix	Diameter		Weight		Min. Bend Radius				Max. Loading			
		in.	mm	lb./kft	kg/km	Install		Long Term		Install		Long Term	
						in.	cm	in.	cm	lbf.	N	lbf.	N
2	ICRK002	0.563	14.3	93	139	8.4	21.5	5.6	14.3	150	660	45	198
4	ICRK004	0.563	14.3	94	140	8.4	21.5	5.6	14.3	150	660	45	198

### FIBER DATA AND SHEATH COLORS

Fiber Type	Part Number Suffix	Berk-Tek Fiber	Core Size	Wavelength (nm)	Maximum Attenuation (dB/km)	Effective Modal Bandwidth @ 850 nm (MHz*km)	Distance (meters)				Sheath Color
<b>Multimode - 62.5 µm Standard, and 50 µm Bend Insensitive</b>							<b>1 GbE</b>	<b>10 GbE</b>	<b>40 GbE</b>	<b>100 GbE</b>	
OM1	CB3510/25	CB	62.5 µm	850/1300	3.5/1.0	200	300	33	N/A	N/A	Orange
OM3	EB3010/25	EB	50 µm	850/1300	3.0/1.0	2000	1000	300	100	70	Aqua
OM4	FB3010/F5	FB	50 µm	850/1300	3.0/1.0	4700	1040	550	150	100	Aqua
OM4+	XB3010/X5	XB	50 µm	850/1300	3.0/1.0	4900	1210	600	300	150	Violet
<b>WideBand Multimode - Bend Insensitive</b>											
OM5	WB3010/W5	WB	50 µm	850-953/1300	3.0/1.0	4700	1040	550	190	100	Lime Green
<b>Single-mode Bend Insensitive - ITU-T G.652.D and G.657.A1 Compliant</b>											
OS2	AB0707	Standard for Tight Buffer	8.3 µm	1310/1550	0.5/0.5	N/A	5000	10000	10000	10000	Yellow

For further support information, visit [leviton.com/ns/support](http://leviton.com/ns/support)

**USA**  
 Network Solutions Headquarters  
 +1 (800) 722 2082  
 infoUSA@leviton.com  
 Berk-Tek Cable: +1 (800) 237 5835  
 berktek.info@leviton.com

**Asia Pacific**  
 +852 3620 2602  
 infoAPAC@leviton.com

**Canada**  
 +1 (800) 461 2002  
 infoCanada@leviton.com

**Europe**  
 +44 (0) 1592 772124  
 infoEurope@leviton.com

**Latin America**  
 MX: +52 (55) 2128 6286  
 LATAM: +52 (55) 2333 5963  
 infoLATAM@leviton.com

**Middle East & Africa**  
 +971 (4) 247 9800  
 infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE TO LEARN MORE.